



# YAEV10L36BOX, Nylon Ring Terminal For 12 - 10 AWG

By Burndy  
Catalog # YAEV10L36BOX



Ring Tongue Copper Tubing Terminal, 1.04 in L, .30 in W, Tin Plated, 600 Volts Max., 105 Deg C Max.

## Features

- Double thick tongue for maximum reliability and electrical capacity plus an extra strong terminal tongue
- Manufactured from one-piece pure electrolytic copper — high conductivity, low resistance with no seams to split plus ductility for excellent crimp forming properties
- Electro-tin plated to provide long-lasting corrosion resistance
- Nylon insulation is locked in place — Insulation will not move or twist off
- 600 volt nylon insulation providing high dielectric strength and stability in demanding oily environmental conditions
- Color Coded providing quick, easy wire size connector selection

## Application

For High Vibration Applications Encountered In Aircraft And Aboard Ships As Well As Motor Lead Applications In Hospitals, Industrials And Generating Plants

## General

Catalog Number	YAEV10L36BOX
Color Code	Yellow
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Military Specification	MS25036
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	INSULUG
Temperature Rating	105°C
Trade Name	INSULUG™
Type	YAEV, Heavy Duty
UPC	781810023082
UPC 12 Digit	7818100230822

## Dimensions

Dimension - B Length fraction 3/10 in

Dimension - B Length inch	0.30 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Hole Size fraction	15/79
Dimension - Hole Size inch	0.19 in
Dimension - L Length Overall mm	1.07 mm
Dimension - Length Overall inch	0.16 in
Dimension - Outside Diameter inch	0.29 in
Dimension - P inch	0.09 in
Dimension - Pad Width inch	0.30 in
Dimension - Strip Length inch	5/16
Dimension - Stud Size inch	#8;#10
Dimension - Z (inch)	0.18 in

## Electrical Ratings

Voltage - Maximum 600 V

## Conductor Related

Conductor - Copper Str Aircraft Size	AN 12;AN 10
Conductor - Copper Str Aircraft Size Range	AN 12-AN 10
Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str Aircraft-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL486</li> <li>• Military Specified (Mil-Spec)</li> </ul>
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM

UL Listed Yes

**Logistics**

Carton Quantity 50

Minimum Pack Quantity 50

Catalogs - BURNDY Master Catalog - Section B - Small  
Compression

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR\_YAEV10L36BOX\_LineArt

Sales Drawings - 50094163

**Product Assets**



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YAEV10L36BOX-SPEC-EN | REV 9/2024