

Nylon Ring Terminal For 6 AWG

By Burndy
Catalog # YAEV6CL2M

Nylon Ring Terminal For 6 AWG.



General

Color Code	Blue
Connector Type	Ring Terminal
Feature - Barrel Style	Belled
Insulation	Y
Insulation Type	Nylon
Material	Copper
Military Specification	MS25036
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	INSULUG™
UPC	781810033524
UPC 12 Digit	7818100335244

Dimensions

Dimension - B Length inch	0.42 in
Dimension - Bolt Size fraction	3/8
Dimension - Length Overall inch	1.68 in
Dimension - N inch	0.3 in
Dimension - P inch	0.13 in
Dimension - Pad Width inch	0.60 in
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.35 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 6
Conductor - Copper Str Aircraft Size Range	AN 6
Conductor - Copper Str Size	6AWG
Conductor Size	6 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">• UL486• Military Specified (Mil-Spec)
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	500
Minimum Pack Quantity	500
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Technical Solutions - BURNDY_YAEV6CL2M_Specsheet](#)

