

# Compression Terminal

By Burndy  
Catalog # [YAG27LTC12FX](#)

3/0 Flex G,H,I,K,M,DLO, 3/0 AWG CU, One Hole, 1/2 Stud Size, Standard Barrel Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Orange Color Code, 14 Die Index.



## Application

Wire Termination

## General

Color Code	Orange
Connector Type	STANDARD BARREL
Die Index	14
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810163542
UPC 12 Digit	7818101635422

## Dimensions

Dimension - B Length inch	1.00 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	1.08 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.62 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.70 in
Dimension - Pad Width inch	1.03 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

## Conductor Related

Conductor - Copper DLO Size	3/0 AWG
Conductor - Copper DLO Size Range	3/0 AWG
Conductor - Copper Flex G Size	"3/0 AWG"
Conductor - Copper Flex G Size Range	3/0 AWG
Conductor - Copper Flex H Size	"3/0 AWG"
Conductor - Copper Flex H Size Range	3/0 AWG
Conductor - Copper Flex I Size	"3/0 AWG"
Conductor - Copper Flex I Size Range	3/0 AWG
Conductor - Copper Flex K Size	"3/0 AWG"
Conductor - Copper Flex K Size Range	3/0 AWG
Conductor - Copper Flex M Size	"3/0 AWG"
Conductor - Copper Flex M Size Range	3/0 AWG
Conductor - Copper Str Compact Size	"3/0 AWG"
Conductor - Copper Str Navy Size	150
Conductor - Copper Str Navy Size Range	150 (61) Navy
Conductor - Copper Str Size	"3/0 AWG"
Conductor - Copper Str Size Range	3/0 AWG
Conductor - CopperWeld Str Size	3/0 E AWG;3/0 EK AWG;3/0 F AWG;3/0 G AWG;3/0 J AWG;3/0 V AWG
Conductor - CopperWeld Str Size Range	3/0 E AWG-3/0 V AWG
Conductor - Material	COPPER
Conductor Size	3/0 AWG
Conductor Type	CODE/FLEX
Wire Size	3/0 AWG

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	UI
UL Listed	Yes

## Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	22200

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)  
[Sales Drawings - 50000268](#)  
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YAG27LTC12FX-SPEC-EN | REV 8/2023