

# Compression Terminal

By Burndy  
Catalog # [YAG28LTC14LD](#)

DISCONTINUED BY YAG28LTC14FXTZ.



## Application

Wire Termination

## General

Color Code	Purple
Connector Type	STANDARD BARREL
Die Index	15
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Lead Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Lead
Trade Name	HYLUG™
Type	Standard Barrel, Lead Plated
UPC	781810036433
UPC 12 Digit	7818100364333

## Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.03 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	57 mm
Dimension - Length Overall inch	2.26 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.77 in
Dimension - Pad Width inch	1.14 in
Dimension - Strip Length inch	1/16 in
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.33 in
Physical Attribute - Tongue Angle	Straight

## Conductor Related

Conductor - Copper DLO Size	4/0 (550/#24) DLO
Conductor - Copper Flex G Size	4/0 AWG
Conductor - Copper Flex H Size	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
Conductor - Copper Flex M Size	4/0 AWG
Conductor - Copper Str Navy Size	200 (61) Navy
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Material	COPPER
Conductor Size	4/0 AWG
Conductor Type	CODE

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
UL Listed	Yes

## Logistics

Minimum Pack Quantity	200
-----------------------	-----

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SE.208132-10](#)  
[Video - HYDENT Compression Terminal Overview Video](#)

Angle

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YAG28LTC14LD-SPEC-EN | REV 8/2023