



Compression Terminal

By Burndy
Catalog # YAG31L2TC12LD

Cu Tubing HYLUG™, 2 Holes, 4.04 inches long.



Application

Wire Termination

General

Color Code	White
Connector Type	STANDARD BARREL
Die Index	17
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Lead Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Lead Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Lead Plated
UPC	781810036266
UPC 12 Digit	7818100362666

Dimensions

Dimension - B Length inch	1.06 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	2.34 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	103 mm
Dimension - Length Overall inch	4.04 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	1.29 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size fraction	1/2
Dimension - Z inch	0.56 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Conductor Related

Conductor - Copper DLO Size	262 KCMIL
Conductor - Copper Flex G Size	250 kcmil
Conductor - Copper Flex H Size	250 kcmil
Conductor - Copper Flex I Size	250 KCMIL
Conductor - Copper Flex K Size	250 kcmil
Conductor - Copper Flex M Size	250 KCMIL
Conductor - Copper Flex M Size Range	250
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Str Size Range	350 kcmil
Conductor - Material	COPPER
Conductor Size	250 KCMIL
Conductor Type	FLEX
Wire Size	250 KCMIL

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	200
-----------------------	-----

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SE207958](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

Voltage - Maximum 35000
Voltage Rating 35 kV



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAG31L2TC12LD-SPEC-EN | REV 8/2023