

# Compression Terminal

By Burndy  
Catalog # YAGB25LTC38FX

Cu Battery Terminal Lug Type, 1/0 AWG, Pink, 12 Index, 3/8 IN Stud, 1-3/16 IN Strip Length.



## Application

Wire Termination

## General

Color Code	Pink
Connector Type	GROUNDING/STARTER LUGS
Die Index	12
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810562840
UPC 12 Digit	7818105628400

## Dimensions

Dimension - Bolt Hole Size inch	0.40 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	61 mm
Dimension - Length Overall inch	2.40 in
Dimension - Pad Width inch	0.87 in
Dimension - Strip Length inch	1-3/16 in
Dimension - Stud Size fraction	3/8
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size	1/0 AWG
Conductor - Copper DLO Size Range	1/0 AWG
Conductor - Copper Flex G Size	1/0 AWG
Conductor - Copper Flex G Size Range	1/0 AWG
Conductor - Copper Flex H Size	1/0 AWG
Conductor - Copper Flex H Size Range	1/0 AWG
Conductor - Copper Flex I Size	1/0 AWG
Conductor - Copper Flex I Size Range	1/0 AWG
Conductor - Copper Flex K Size	1/0 AWG
Conductor - Copper Flex K Size Range	1/0 AWG
Conductor - Copper Flex M Size	1/0 AWG
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE/FLEX
Wire Size	1/0 AWG

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	200
Minimum Pack Quantity	20

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50004537](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YAGB25LTC38FX-SPEC-EN | REV 8/2023