



YAGB28LTC12FXOEM, Battery Terminal, 4/0 AWG, 1-Hole, 1/2" Stud

By Burndy
Catalog # [YAGB28LTC12FXOEM](#)



Cu Battery Terminal Lug Type, 4/0 AWG, 1/2 in Stud, Connector Color Code- Yellow, Die Color Code- Purple, 1-Hole, 15 Die Index, Tin Plated, Terminal, Standard Barrel.

Application

Wire Termination

General

Catalog Number	YAGB28LTC12FXOEM
Color Code	Purple
Connector Type	GROUNDING/STARTER LUGS
Die Index	15
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electroplated
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810526002
UPC 12 Digit	7818105260022

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	74 mm
Dimension - Length Overall inch	2.90 in
Dimension - Strip Length inch	1-3/16 in
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	4/0 AWG
Conductor - Copper DLO Size Range	4/0 AWG
Conductor - Copper Flex G Size	4/0 AWG
Conductor - Copper Flex G Size Range	4/0 AWG
Conductor - Copper Flex H Size	4/0 AWG
Conductor - Copper Flex H Size Range	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
Conductor - Copper Flex I Size Range	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
Conductor - Copper Flex K Size Range	4/0 AWG
Conductor - Copper Flex M Size	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Material	COPPER
Conductor Size	4/0 AWG
Conductor Type	CODE/FLEX
Wire Size	4/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

Product Assets

[3D Models - YAGB28LTC12FXOEM_MODEL-STEP](#)

[3D Models - YAGB28LTC12FXOEM_MODEL-PDF](#)

[3D Models - YAGB28LTC12FXOEM_MODEL-IGES](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section C - Compression](#)

[Connections](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - 30008293](#)

[Specifications - YAGB28LTC12FXOEM](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAGB28LTC12FXOEM-SPEC-EN | REV 8/2024