




## YAGB28LTC516FXOEM, Battery Terminal, 4/0 AWG, 1-Hole, 5/16" Stud

By Burndy  
Catalog # [YAGB28LTC516FXOEM](#)



1 Hole HYLUG™ Cu Battery Terminal, 4/0 AWG, 5/16" stud, 2.56" L, 1.10" W, Yellow.

### Application

Wire Termination

### General

Catalog Number	YAGB28LTC516FXOEM
Color Code	Purple
Connector Type	GROUNDING/STARTER LUGS
Die Index	15
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810531099
UPC 12 Digit	7818105310999

### Dimensions

Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - Length Overall inch	2.56 in
Dimension - Pad Width inch	1.1 in
Dimension - Strip Length inch	1-3/16 in
Dimension - Stud Size fraction	5/16
Dimension - Stud Size inch	5/16 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper DLO Size	4/0 AWG
Conductor - Copper DLO Size Range	4/0 AWG
Conductor - Copper Flex G Size	4/0 AWG
Conductor - Copper Flex G Size Range	4/0 AWG
Conductor - Copper Flex H Size	4/0 AWG
Conductor - Copper Flex H Size Range	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
Conductor - Copper Flex I Size Range	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
Conductor - Copper Flex K Size Range	4/0 AWG
Conductor - Copper Flex M Size	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Material	COPPER
Conductor Size	4/0 AWG
Conductor Type	CODE/FLEX
Wire Size	4/0 AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

### Logistics

Minimum Pack Quantity	100
-----------------------	-----

## Product Assets

[3D Models - YAGB28LTC516FXOEM\\_MODEL-IGES](#)

[3D Models - YAGB28LTC516FXOEM\\_MODEL-PDF](#)

[3D Models - YAGB28LTC516FXOEM\\_MODEL-STEP](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section C - Compression](#)

[Connections](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - 30008293](#)

[Specifications - YAGB28LTC516FXOEM](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YAGB28LTC516FXOEM-SPEC-EN | REV 8/2024