

# Compression Terminal

By Burndy  
Catalog # YAGB2CLTC10FX

1 Hole HYLUG™ Cu Battery Terminal, #2 AWG, #10 stud, 2.09" L, 0.81" W, Green.



## Application

Wire Termination

## General

|                                      |                        |
|--------------------------------------|------------------------|
| Color Code                           | Brown                  |
| Connector Type                       | GROUNDING/STARTER LUGS |
| Die Index                            | 10                     |
| Finish Type                          | Tin-Plated             |
| Material                             | COPPER                 |
| Physical Attribute - Number of Holes | 1                      |
| Temperature Rating                   | 194                    |
| Trade Name                           | HYLUG™                 |
| Type                                 | OEM Terminals          |
| UPC                                  | 781810562772           |
| UPC 12 Digit                         | 7818105627722          |

## Dimensions

|                                   |          |
|-----------------------------------|----------|
| Dimension - Bolt Size fraction    | #8-#10   |
| Dimension - Bolt Size inch        | 0.21     |
| Dimension - Hole Size fraction    | #10      |
| Dimension - Hole Size inch        | 0.21     |
| Dimension - Hole Size mm          | 5.3 mm   |
| Dimension - L Length Overall mm   | 53 mm    |
| Dimension - Length Overall inch   | 2.09 in  |
| Dimension - Pad Width inch        | 0.81 in  |
| Dimension - Strip Length inch     | 15/16 in |
| Dimension - Stud Size fraction    | #10      |
| Dimension - Stud Size inch        | #10      |
| Physical Attribute - Tongue Angle | Straight |

## Electrical Ratings

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating    | 35 kV |

## Conductor Related

|                                      |           |
|--------------------------------------|-----------|
| Conductor - Copper DLO Size          | 2 AWG     |
| Conductor - Copper DLO Size Range    | 2 AWG     |
| Conductor - Copper Flex G Size       | 2 AWG     |
| Conductor - Copper Flex G Size Range | 2 AWG     |
| Conductor - Copper Flex H Size       | 2 AWG     |
| Conductor - Copper Flex H Size Range | 2 AWG     |
| Conductor - Copper Flex I Size       | 2 AWG     |
| Conductor - Copper Flex I Size Range | 2 AWG     |
| Conductor - Copper Flex K Size       | 2 AWG     |
| Conductor - Copper Flex K Size Range | 2 AWG     |
| Conductor - Copper Flex M Size       | 2 AWG     |
| Conductor - Copper Str Size          | 2 AWG     |
| Conductor - Copper Str Size Range    | 2 AWG     |
| Conductor - Material                 | COPPER    |
| Conductor Size                       | 2 AWG     |
| Conductor Type                       | CODE/FLEX |
| Wire Size                            | 2 AWG     |

## Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

## Logistics

|                       |     |
|-----------------------|-----|
| Carton Quantity       | 200 |
| Minimum Pack Quantity | 20  |

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50004537](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YAGB2CLTC10FX-SPEC-EN | REV 8/2023