



## YAGB2CLTC14FX, Battery Terminal, 2 AWG, 1-Hole, 1/4" Stud

By Burndy  
Catalog # [YAGB2CLTC14FX](#)

1 Hole HYLUG™ Cu Battery Terminal, #2 AWG, 1/4" stud, 2.09" L, 0.81" W, Green.



### Features

- Color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Not UL Listed but tested and met UL486A-486B pullout requirements

### Application

Wire Termination

### General

Catalog Number	YAGB2CLTC14FX
Color Code	Brown
Connector Type	GROUNDING/STARTER LUGS
Die Index	10
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810562789
UPC 12 Digit	7818105627899

### Dimensions

Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	53 mm
Dimension - Length Overall inch	2.09 in
Dimension - Pad Width inch	0.81 in
Dimension - Strip Length inch	15/16 in
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper DLO Size	2 AWG
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper Flex G Size	2 AWG
Conductor - Copper Flex G Size Range	2 AWG
Conductor - Copper Flex H Size	2 AWG
Conductor - Copper Flex H Size Range	2 AWG
Conductor - Copper Flex I Size	2 AWG
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex M Size	2 AWG
Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG
Conductor Type	CODE/FLEX
Wire Size	2 AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	200
Minimum Pack Quantity	20

## Product Assets

[Catalogs - BURNDY Master Catalog - Section C - Compression](#)

[Connections](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - 50004537](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YAGB2CLTC14FX-SPEC-EN | REV 8/2024