

Compression Terminal

By Burndy
Catalog # YAGB4CLTC10FX

1 Hole Cu Tubing HYLUG™, #4 AWG, #10 stud, 1.36" L, 0.55" W.



Application

Wire Termination

General

Color Code	Gray
Connector Type	GROUNDING/STARTER LUGS
Die Index	6
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810562727
UPC 12 Digit	7818105627277

Dimensions

Dimension - Bolt Size fraction	#8-#10
Dimension - Bolt Size inch	0.21
Dimension - Hole Size fraction	#10
Dimension - Hole Size inch	0.21
Dimension - Hole Size mm	5.3 mm
Dimension - L Length Overall mm	35 mm
Dimension - Length Overall inch	1.36 in
Dimension - Pad Width inch	0.55 in
Dimension - Strip Length inch	9/16 in
Dimension - Stud Size fraction	#10
Dimension - Stud Size inch	#10
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	4 AWG
Conductor - Copper DLO Size Range	4 AWG
Conductor - Copper Flex G Size	4 AWG
Conductor - Copper Flex G Size Range	4 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Copper Flex H Size Range	4 AWG
Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex I Size Range	4 AWG
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex K Size Range	4 AWG
Conductor - Copper Flex M Size	4 AWG
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor - Material	COPPER
Conductor Size	4 AWG
Conductor Type	CODE/FLEX
Wire Size	4 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	20
Minimum Pack Quantity	20

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50015971](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAGB4CLTC10FX-SPEC-EN | REV 8/2023