

Compression Terminal

By Burndy
Catalog # [YAGB4CLTC12FXOEM](#)

1 Hole HYLUG™ Cu Battery Terminal, 4 AWG, 1/2" stud, 1.97" L, 0.75" W, Grey.



Application

Wire Termination

General

Color Code	Gray
Connector Type	GROUNDING/STARTER LUGS
Die Index	6
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810563113
UPC 12 Digit	7818105631133

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	50 mm
Dimension - Length Overall inch	1.97 in
Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	15/16 in
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	4 AWG
Conductor - Copper DLO Size Range	4 AWG
Conductor - Copper Flex G Size	4 AWG
Conductor - Copper Flex G Size Range	4 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Copper Flex H Size Range	4 AWG
Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex I Size Range	4 AWG
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex K Size Range	4 AWG
Conductor - Copper Flex M Size	4 AWG
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor - Material	COPPER
Conductor Size	4 AWG
Conductor Type	CODE/FLEX
Wire Size	4 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

Logistics

Minimum Pack Quantity	200
-----------------------	-----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50004537](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YAGB4CLTC12FXOEM-SPEC-EN | REV 5/2024