

Compression Terminal

By Burndy
Catalog # [YAGB4CLTC516FXOEM](#)

Cu Tubing Hylug, #4 AWG, 5/16 IN Stud.



Application

Wire Termination

General

| | |
|--------------------------------------|------------------------|
| Color Code | Gray |
| Connector Type | GROUNDING/STARTER LUGS |
| Construction Material - Main | Copper |
| Die Index | 6 |
| EU RoHS Indicator | Contact Manufacturer |
| Finish Type | Electro Tin plated |
| Material | COPPER |
| Physical Attribute - Number of Holes | 1 |
| Plating Type | Tin - Electro Plated |
| Sub Brand | HYLUG |
| Temperature Rating | 194 |
| Trade Name | HYLUG™ |
| Type | OEM Terminals |
| UPC | 781810547656 |
| UPC 12 Digit | 7818105476566 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - Bolt Size fraction | 5/16 |
| Dimension - Bolt Size inch | 0.3125 |
| Dimension - Hole Size fraction | 5/16 |
| Dimension - Hole Size inch | 0.38 |
| Dimension - Hole Size mm | 10 mm |
| Dimension - L Length Overall mm | 37 mm |
| Dimension - Length Overall inch | 1.45 in |
| Dimension - Pad Width inch | 0.61 in |
| Dimension - Stud Size fraction | 5/16 |
| Dimension - Stud Size inch | 5/16 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating | 35 kV |

Conductor Related

| | |
|--------------------------------------|-----------|
| Conductor - Copper DLO Size | 4 AWG |
| Conductor - Copper DLO Size Range | 4 AWG |
| Conductor - Copper Flex G Size | 4 AWG |
| Conductor - Copper Flex G Size Range | 4 AWG |
| Conductor - Copper Flex H Size | 4 AWG |
| Conductor - Copper Flex H Size Range | 4 AWG |
| Conductor - Copper Flex I Size | 4 AWG |
| Conductor - Copper Flex I Size Range | 4 AWG |
| Conductor - Copper Flex K Size | 4 AWG |
| Conductor - Copper Flex K Size Range | 4 AWG |
| Conductor - Copper Flex M Size | 4 AWG |
| Conductor - Copper Str Size | 4 AWG |
| Conductor - Copper Str Size Range | 4 AWG |
| Conductor - Material | COPPER |
| Conductor Size | 4 AWG |
| Conductor Type | CODE/FLEX |
| Wire Size | 4 AWG |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| Standards - RoHS Compliant | Yes |
| UL Listed | No |

Logistics

| | |
|-----------------------|-----|
| Minimum Pack Quantity | 200 |
|-----------------------|-----|

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 30008293](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAGB4CLTC516FXOEM-SPEC-EN | REV 8/2023