



YAK34A2G2, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy

Catalog # [YAK34A2G2](#)



Cast Al Straight Stacking Lug, 2-NEMA Holes, 500 kcmil Al, 500 kcmil Al Compressed, 0.56" Hole Dia.

Application

For Aluminum

General

Catalog Number	YAK34A2G2
Connector Type	Terminal
Die Index	317;705
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Aluminum Alloy
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YAK-A-2G, Stacking Lug
UPC	781810802281
UPC 12 Digit	781810802281

Dimensions

Dimension - B Length inch	2.41 in
Dimension - Bolt Hole Size inch	0.50 in
Dimension - D inch	3.06 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	197 mm
Dimension - Length Overall inch	7.75 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	2-1/2 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YAK-A-2G_LineArt](#)
[Sales Drawings - SD59493-01](#)
[Specifications - YAK34A2G2](#)



A Hubbell brand