



## YAK44A2NG8, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy  
Catalog # [YAK44A2NG8](#)



Cast Al Terminal Offset Lug, Stacking Hylug, 2 Holes, 1000 kcmil,  
302 Index, 0.56" Hole Dia.

### General

Catalog Number	YAK44A2NG8
Die Index	302
Feature - Barrel Style	Chamfered
Material	Aluminum Alloy
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810187555
UPC 12 Digit	7818101875555

### Dimensions

Dimension - B Length inch	2.97 in
Dimension - Bolt Hole Size inch	0.50 in
Dimension - D inch	3.18 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	226 mm
Dimension - Length Overall inch	8.88 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.84 in
Dimension - Pad Width inch	1.62 in
Physical Attribute - Tongue Angle	Straight

### Conductor Related

Conductor - AL Str Size	1000 kcmil
Conductor - AL Str Size Range	1000 kcmil

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	5
-----------------------	---

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YAK-A-2G\\_LineArt](#)
- [Sales Drawings - SC..074256-01](#)
- [Specifications - YAK44A2NG8](#)