

Compression Terminal

By Burndy
Catalog # [YAL30T12B](#)

Copper Compression Lug, 1 Hole w/ Inspection Window, 300 kcmil, 1/2" Stud, Short Barrel, Belled End, Tin Plated.



Application

Wire Termination

General

Color Code	White
Connector Type	STANDARD BARREL
Die Index	17
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810417225

Dimensions

Dimension - B Length fraction	1-1/25 in
Dimension - B Length inch	1.04 in
Dimension - Bolt Hole Size	0.53 in
inch	
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - L Length Overall	72 mm
mm	
Dimension - Length Overall	2.82 in
inch	
Dimension - Outside Diameter	0.81 in
inch	
Dimension - Pad Width inch	1.20 in
Dimension - Strip Length inch	1-1/8 in
Dimension - Stud Size inch	1/2 in
Physical Attribute - Tongue	Straight
Angle	

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	N/A
Range	
Conductor - Copper Str Size	300 KCMIL
Conductor - Copper Str Size	300 kcmil
Range	
Conductor - Material	COPPER
Conductor Size	300 KCMIL
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	10

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50054915](#)

