

# Compression Terminal

By Burndy  
Catalog # YALB102M4

Cu Compression Metric Lug, 2 Hole, W/o Inspection Window, 10 mm, M4 Stud, 44.5 mm Spacing, Long Barrel, 22 mm Wire Strip Length.



## Application

Metric Wire Termination

## General

Connector Type	METRIC
Die Index	49
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810639207
UPC 12 Digit	7818106392077

## Dimensions

Dimension - B Length inch	0.81 in
Dimension - Bolt Size fraction	#8
Dimension - Hole Size fraction	#8
Dimension - Hole Size inch	0.18
Dimension - Hole Size mm	4.6 mm
Dimension - L Length Overall mm	82.6 mm
Dimension - Length Overall inch	3.25 in
Dimension - Pad Width inch	0.39 in
Dimension - Strip Length inch	0.87 in
Dimension - Stud Size fraction	#8
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	10 mm <sup>2</sup>
Conductor - Material	COPPER
Conductor Size	10 mm <sup>2</sup>
Conductor Type	CLASS 2

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

## Product Assets

[3D Models - YALB102M4\\_MODEL-STEP](#)  
[3D Models - YALB102M4\\_MODEL-IGES](#)  
[3D Models - YALB102M4\\_MODEL-PDF](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50025967](#)