

# Compression Terminal

By Burndy  
Catalog # YALB1202M14

Cu Compression Metric Lug, 2 Hole, W/o Inspection Window, 120 mm, M14 Stud, 44.5 mm Spacing, Long Barrel, 43 mm Wire Strip Length.



## Application

Metric Wire Termination

## General

Connector Type	METRIC
Die Index	15
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810639634
UPC 12 Digit	7818106396344

## Dimensions

Dimension - B Length inch	1.62 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	129 mm
Dimension - Pad Width inch	1.14 in
Dimension - Strip Length inch	1.69 in
Dimension - Stud Size fraction	1/2
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	120 mm <sup>2</sup>
Conductor - Material	COPPER
Conductor Size	120 mm <sup>2</sup>
Conductor Type	CLASS 2

## Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	9600

## Product Assets

[3D Models - YALB1202M14\\_MODEL-IGES](#)  
[3D Models - YALB1202M14\\_MODEL-PDF](#)  
[3D Models - YALB1202M14\\_MODEL-STEP](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YALBM\\_LineArt](#)  
[Sales Drawings - 50025967](#)