

## YALB1202M20, Compression Terminal

By Burndy  
Catalog # [YALB1202M20](#)



Cu Compression Metric Lug, 2 Hole, W/o Inspection Window, 120 mm, M20 Stud, 44.5 mm Spacing, Long Barrel, 43 mm Wire Strip Length.

### Application

Metric Wire Termination

### General

Catalog Number	YALB1202M20
Connector Type	METRIC
Die Index	15
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810639658
UPC 12 Digit	7818106396588

### Dimensions

Dimension - B Length inch	1.62 in
Dimension - Bolt Size fraction	7/8
Dimension - Bolt Size inch	0.88
Dimension - Hole Size fraction	7/8
Dimension - Hole Size inch	0.94
Dimension - Hole Size mm	23.8 mm
Dimension - L Length Overall mm	145.5 mm
Dimension - Pad Width inch	1.20 in
Dimension - Strip Length inch	1.69 in
Dimension - Stud Size fraction	7/8
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper Str Size	120 mm2
Conductor - Material	COPPER
Conductor Size	120 mm2
Conductor Type	CLASS 2

### Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	10
-----------------------	----

### Product Assets

[3D Models - YALB1202M20\\_MODEL-IGES](#)  
[3D Models - YALB1202M20\\_MODEL-STEP](#)  
[3D Models - YALB1202M20\\_MODEL-PDF](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YALBM\\_LineArt](#)  
[Sales Drawings - 50025967](#)  
[Specifications - YALB1202M20](#)