

YALB150M10, Compression Terminal

By Burndy
Catalog # [YALB150M10](#)

Cu Compression Metric Lug, 1 Hole, W/o Inspection Window, 150 mm, M10 Stud, Long Barrel.



Application

Metric Wire Termination

General

Catalog Number	YALB150M10
Connector Type	METRIC
Die Index	17
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638804
UPC 12 Digit	7818106388044

Dimensions

Dimension - B Length inch	2.00 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	87.3 mm
Dimension - Length Overall inch	3.44 in
Dimension - Pad Width inch	1.20 in
Dimension - Strip Length inch	2.05 in
Dimension - Stud Size fraction	3/8
Dimension - Z (inch)	0.42 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	150 mm ²
Conductor - Material	COPPER
Conductor Size	150 mm ²
Conductor Type	CLASS 2

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

- [3D Models - YALB150M10_MODEL-IGES](#)
- [3D Models - YALB150M10_MODEL-STEP](#)
- [3D Models - YALB150M10_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_yav2m_lineart](#)
- [Sales Drawings - 50025611](#)
- [Specifications - YALB150M10](#)