

YALB16M6, Compression Terminal

By Burndy
Catalog # [YALB16M6](#)

Cu Compression Metric Lug, 1 Hole, W/o Inspection Window, 16 mm, M6 Stud, Long Barrel.



Application

Metric Wire Termination

General

Catalog Number	YALB16M6
Connector Type	METRIC
Die Index	7
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638422
UPC 12 Digit	7818106384222

Dimensions

Dimension - B Length inch	1.12 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	51.9 mm
Dimension - Length Overall inch	2.05 in
Dimension - Pad Width inch	0.48 in
Dimension - Strip Length inch	1.18 in
Dimension - Stud Size fraction	1/4
Dimension - Z (inch)	0.33 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	16 mm ²
Conductor - Material	COPPER
Conductor Size	16 mm ²
Conductor Type	CLASS 2

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	50

Product Assets

[3D Models - YALB16M6_MODEL-STEP](#)
[3D Models - YALB16M6_MODEL-IGES](#)
[3D Models - YALB16M6_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_yav2m_lineart](#)
[Sales Drawings - 50025611](#)
[Specifications - YALB16M6](#)