

Compression Terminal

By Burndy
Catalog # YALB2402M14

Cu Compression Metric Lug, 2 Hole, W/o Inspection Window, 240 mm, M14 Stud, 44.5 mm Spacing, Long Barrel, 59 mm Wire Strip Length.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	20
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810639801
UPC 12 Digit	7818106398011

Dimensions

Dimension - B Length inch	2.25 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	150.5 mm
Dimension - Length Overall inch	5.93 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	2.32 in
Dimension - Stud Size fraction	1/2
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	240 mm ²
Conductor - Material	COPPER
Conductor Size	240 mm ²
Conductor Type	CLASS 2

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

[3D Models - YALB2402M14_MODEL-PDF](#)
[3D Models - YALB2402M14_MODEL-STEP](#)
[3D Models - YALB2402M14_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50025967](#)