



## YALB3002M14, Compression Terminal

By Burndy  
Catalog # [YALB3002M14](#)



Cu Compression Metric Lug, 2 Hole, W/o Inspection Window, 300 mm, M14 Stud, 44.5 mm Spacing, Long Barrel, 70 mm Wire Strip Length.

### Application

Metric Wire Termination

### General

|                |                      |
|----------------|----------------------|
| Catalog Number | YALB3002M14          |
| Connector Type | METRIC               |
| Die Index      | 22                   |
| Finish Type    | Tin-Plated           |
| Material       | COPPER               |
| Plated         | Y                    |
| Plating Type   | Tin - Electro Plated |
| Trade Name     | HYLUG™               |
| Type           | Metric Terminals     |
| UPC            | 781810639856         |
| UPC 12 Digit   | 7818106398566        |

### Dimensions

|                                   |          |
|-----------------------------------|----------|
| Dimension - B Length inch         | 2.69 in  |
| Dimension - Bolt Size fraction    | 1/2      |
| Dimension - Bolt Size inch        | 0.5      |
| Dimension - Hole Size fraction    | 1/2      |
| Dimension - Hole Size inch        | 0.56     |
| Dimension - Hole Size mm          | 14 mm    |
| Dimension - L Length Overall mm   | 163.5 mm |
| Dimension - Length Overall inch   | 6.44 in  |
| Dimension - Pad Width inch        | 1.74 in  |
| Dimension - Strip Length inch     | 2.76 in  |
| Dimension - Stud Size fraction    | 1/2      |
| Physical Attribute - Tongue Angle | Straight |

### Electrical Ratings

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating    | 35 kV |

### Conductor Related

|                             |         |
|-----------------------------|---------|
| Conductor - Copper Str Size | 300 mm2 |
| Conductor - Material        | COPPER  |
| Conductor Size              | 300 mm2 |
| Conductor Type              | CLASS 2 |

### Certifications And Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Standards - RoHS Compliance Status | CM |

### Logistics

|                       |   |
|-----------------------|---|
| Carton Quantity       | 5 |
| Minimum Pack Quantity | 5 |

### Product Assets

- [3D Models - YALB3002M14\\_MODEL-STEP](#)
- [3D Models - YALB3002M14\\_MODEL-PDF](#)
- [3D Models - YALB3002M14\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YALBM\\_LineArt](#)
- [Sales Drawings - 50025967](#)
- [Specifications - YALB3002M14](#)