

Compression Terminal

By Burndy
Catalog # YALB300F2M20

Cu Compression Metric Lug, 2 Hole, W/o Inspection Window, 300 mm, M20 Stud, 44.5 mm Spacing, Long Barrel, 73 mm Wire Strip Length.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	22
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810642894
UPC 12 Digit	7818106428944

Dimensions

Dimension - B Length inch	2.81 in
Dimension - Bolt Size fraction	7/8
Dimension - Bolt Size inch	0.88
Dimension - Hole Size fraction	7/8
Dimension - Hole Size inch	0.94
Dimension - Hole Size mm	23.8 mm
Dimension - L Length Overall mm	184.5 mm
Dimension - Length Overall inch	7.27 in
Dimension - Pad Width inch	1.84 in
Dimension - Strip Length inch	2.87 in
Dimension - Stud Size fraction	7/8
Dimension - Z inch	0.89 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	300 mm ²
Conductor - Material	COPPER
Conductor Size	300 mm ²
Conductor Type	CLASS 2

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

[3D Models - YALB300F2M20_MODEL-STEP](#)
[3D Models - YALB300F2M20_MODEL-PDF](#)
[3D Models - YALB300F2M20_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50025984](#)