



# Compression Terminal

By Burndy  
Catalog # [YALB300FM10](#)

Cu Compression Metric Lug, 1 Hole, W/o Inspection Window, 300 mm, M10 Stud, Long Barrel, 73 mm Wire Strip Length.



## Application

Metric Wire Termination

## General

Connector Type	METRIC
Die Index	22
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810641941
UPC 12 Digit	7818106419411

## Dimensions

Dimension - B Length inch	2.81 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	114.7 mm
Dimension - Length Overall inch	4.52 in
Dimension - Pad Width inch	1.84 in
Dimension - Strip Length inch	2.87 in
Dimension - Stud Size fraction	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	300 mm <sup>2</sup>
Conductor - Material	COPPER
Conductor Size	300 mm <sup>2</sup>
Conductor Type	CLASS 5

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	5
-----------------------	---

## Product Assets

[3D Models - YALB300FM10\\_MODEL-PDF](#)  
[3D Models - YALB300FM10\\_MODEL-STEP](#)  
[3D Models - YALB300FM10\\_MODEL-IGES](#)  
[Sales Drawings - 50025865](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YALB300FM10-SPEC-EN | REV 8/2023