



YALB300FM16, Compression Terminal

By Burndy
Catalog # [YALB300FM16](#)



Cu Compression Metric Lug, 1 Hole, W/o Inspection Window, 300 mm, M16 Stud, Long Barrel, 73 mm Wire Strip Length.

Application

Metric Wire Termination

General

Catalog Number	YALB300FM16
Connector Type	METRIC
Die Index	22
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810641972
UPC 12 Digit	7818106419722

Dimensions

Dimension - B Length inch	2.81 in
Dimension - Bolt Size fraction	5/8
Dimension - Bolt Size inch	0.63
Dimension - Hole Size fraction	5/8
Dimension - Hole Size inch	0.69
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	127.4 mm
Dimension - Length Overall inch	5.02 in
Dimension - Pad Width inch	1.84 in
Dimension - Strip Length inch	2.87 in
Dimension - Stud Size fraction	5/8
Dimension - Z (inch)	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	300 mm ²
Conductor - Material	COPPER
Conductor Size	300 mm ²
Conductor Type	CLASS 5

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

- [3D Models - YALB300FM16_MODEL-STEP](#)
- [3D Models - YALB300FM16_MODEL-IGES](#)
- [3D Models - YALB300FM16_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YALB2M_LineArt](#)
- [Sales Drawings - 50025865](#)
- [Specifications - YALB300FM16](#)