

Compression Terminal

By Burndy
Catalog # YALB35M5

Cu Compression Metric Lug, 1 Hole, W/o Inspection Window, 35 mm, M5 Stud, Long Barrel.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	10
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638514
UPC 12 Digit	7818106385144

Dimensions

Dimension - B Length inch	1.38 in
Dimension - Bolt Size fraction	#8-#10
Dimension - Bolt Size inch	0.21
Dimension - Hole Size fraction	#10
Dimension - Hole Size inch	0.21
Dimension - Hole Size mm	5.3 mm
Dimension - L Length Overall mm	57.6 mm
Dimension - Length Overall inch	2.27 in
Dimension - Pad Width inch	0.68 in
Dimension - Strip Length inch	1.46 in
Dimension - Stud Size fraction	#10
Dimension - Z inch	0.27 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	35 mm ²
Conductor - Material	COPPER
Conductor Size	35 mm ²
Conductor Type	CLASS 2

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	50
-----------------------	----

Product Assets

[3D Models - YALB35M5_MODEL-STEP](#)
[3D Models - YALB35M5_MODEL-PDF](#)
[3D Models - YALB35M5_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50025611](#)