

Compression Terminal

By Burndy
Catalog # YALB50M12

Cu Compression Metric Lug, 1 Hole, W/o Inspection Window, 50 mm, M12 Stud, Long Barrel.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	12
Finish Type	Tin-Plated
Material	COPPER
Plated	Yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638583
UPC 12 Digit	7818106385833

Dimensions

Dimension - B Length inch	1.38 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	71.9 mm
Dimension - Length Overall inch	2.83 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	1.46 in
Dimension - Stud Size fraction	1/2
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	50 mm2
Conductor - Material	COPPER
Conductor Size	50 mm2
Conductor Type	CLASS 2

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	20
-----------------------	----

Product Assets

[3D Models - YALB50M12_MODEL-PDF](#)
[3D Models - YALB50M12_MODEL-IGES](#)
[3D Models - YALB50M12_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50025611](#)