



# YALB630F2M12, Compression Terminal

By Burndy  
Catalog # [YALB630F2M12](#)

Cu Compression Metric Lug Terminal, 2 Holes, 630 mm, M12 Stud, Long Barrel.



## Application

Metric Wire Termination

## General

Catalog Number	YALB630F2M12
Connector Type	METRIC
Die Index	29
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810643044
UPC 12 Digit	7818106430444

## Dimensions

Dimension - B Length inch	3.19 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	186.9 mm
Dimension - Length Overall inch	7.36 in
Dimension - Pad Width inch	2.69 in
Dimension - Strip Length inch	3.27 in
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.55 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	630 mm2
Conductor - Material	COPPER
Conductor Size	630 mm2
Conductor Type	CLASS 2

## Certifications And Compliance

Certification - CSA Approved	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	2
-----------------------	---

## Product Assets

- [3D Models - YALB630F2M12\\_MODEL-PDF](#)
- [3D Models - YALB630F2M12\\_MODEL-STEP](#)
- [3D Models - YALB630F2M12\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_yavm\\_lineart](#)
- [Sales Drawings - 50025984](#)
- [Specifications - YALB630F2M12](#)