

Compression Terminal

By Burndy
Catalog # [YALB70FM14](#)

Cu Compression Metric Lug, 1 Hole, W/o Inspection Window, 70 mm, M14 Stud, Long Barrel, 40 mm Wire Strip Length.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	13
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810641620
UPC 12 Digit	7818106416200

Dimensions

Dimension - B Length inch	1.50 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	79 mm
Dimension - Length Overall inch	3.11 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	1.57 in
Dimension - Stud Size fraction	1/2
Dimension - Z inch	0.57 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	70 mm ²
Conductor - Material	COPPER
Conductor Size	70 mm ²
Conductor Type	CLASS 5

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	20
-----------------------	----

Product Assets

[3D Models - YALB70FM14_MODEL-STEP](#)
[3D Models - YALB70FM14_MODEL-PDF](#)
[3D Models - YALB70FM14_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50025865](#)