

# Compression Terminal

By Burndy  
Catalog # [YALB952M14](#)

Cu Compression Metric Lug, 2 Hole, W/o Inspection Window, 95 mm, M14 Stud, 44.5 mm Spacing, Long Barrel, 40 mm Wire Strip Length.



## Application

Metric Wire Termination

## General

Connector Type	METRIC
Die Index	14
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810639573
UPC 12 Digit	7818106395733

## Dimensions

Dimension - B Length inch	1.50 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	123 mm
Dimension - Length Overall inch	4.86 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	1.57 in
Dimension - Stud Size fraction	1/2
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	95 mm2
Conductor - Material	COPPER
Conductor Size	95 mm2
Conductor Type	CLASS 2

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	10
-----------------------	----

## Product Assets

[3D Models - YALB952M14\\_MODEL-PDF](#)  
[3D Models - YALB952M14\\_MODEL-STEP](#)  
[3D Models - YALB952M14\\_MODEL-IGES](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50025967](#)