



## YALB952M8, Compression Terminal

By Burndy  
Catalog # [YALB952M8](#)

Cu Compression Metric Lug, 2 Hole, W/o Inspection Window, 95 mm, M8 Stud, 44.5 mm Spacing, Long Barrel, 40 mm Wire Strip Length.



### Application

Metric Wire Termination

### General

Catalog Number	YALB952M8
Connector Type	METRIC
Die Index	14
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810639542
UPC 12 Digit	7818106395422

### Dimensions

Dimension - B Length inch	1.50 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	113 mm
Dimension - Length Overall inch	4.45 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	1.57 in
Dimension - Stud Size fraction	5/16
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper Str Size	95 mm <sup>2</sup>
Conductor - Material	COPPER
Conductor Size	95 mm <sup>2</sup>
Conductor Type	CLASS 2

### Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	10
-----------------------	----

### Product Assets

- [3D Models - YALB952M8\\_MODEL-IGES](#)
- [3D Models - YALB952M8\\_MODEL-PDF](#)
- [3D Models - YALB952M8\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YALBM\\_LineArt](#)
- [Sales Drawings - 50025967](#)
- [Specifications - YALB952M8](#)