

# YAS25RN, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy  
Catalog # YAS25RN



Aluminum Stacking Terminal- Straight Lug, 1/0 Al-Cu, 1/0 ACSR, 1 Hole, Yellow.

## General

Catalog Number	YAS25RN
Color Code	Yellow
Die Index	BG;243;K-5/8-1;CSA22
Feature - Barrel Style	Chamfered
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810093931
UPC 12 Digit	7818100939311

## Dimensions

Dimension - B Length inch	0.96 in
Dimension - Hole Size inch	0.56 in
Dimension - Inside Diameter inch	0.42 in
Dimension - L Length Overall mm	77 mm
Dimension - Length Overall inch	3.05 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.65 in
Dimension - P inch	1.29 in
Dimension - Pad Width inch	0.90 in
Dimension - Strip Length inch	1-3/32 in
Dimension - Z (inch)	1.10 in

## Conductor Related

Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG
Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	20
Minimum Pack Quantity	20
Pallet Quantity	19200

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SE209225-01](#)  
[Specifications - YAS25RN](#)