

YAS26R2N, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # YAS26R2N



Straight Stacking Lug, Al Tubing, 2-NEMA Holes, 2/0 AWG
Cu/Al,ACSR, Gray, 0.56" Hole Dia.

General

Catalog Number	YAS26R2N
Color Code	Gray
Connector Type	Terminal
Die Index	249;840;CSA24
Feature - Barrel Style	Tapered
Material	Aluminum
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810050248
UPC 12 Digit	7818100502488

Dimensions

Dimension - B Length inch	1.47 in
Dimension - D inch	3.76 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	148 mm
Dimension - Length Overall inch	5.83 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	1.24 in
Dimension - Strip Length inch	1-19/32 in
Dimension - Z (inch)	1.38 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - ACSR Str Size	2/0 (6/1) Quail AWG
Conductor - ACSR Str Size Range	2/0 (6/1) Quail AWG
Conductor - AL Str Size	2/0 AWG
Conductor - AL Str Size Range	2/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	5920

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YAS25R2N_LineArt](#)
[Sales Drawings - SE208417](#)
[Specifications - YAS26R2N](#)