

YAS361R2N, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAS361R2N](#)



Straight Stacking Lug, Al Tubing, 2-NEMA Holes, 500 Al/Cu, 477 ACSR, Pink, 0.56" Hole Dia.

General

Catalog Number	YAS361R2N
Color Code	Pink
Connector Type	Terminal
Die Index	608;722;K-1-5/16;CSA28
Feature - Barrel Style	Chamfered
Material	Aluminum Alloy
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810052006
UPC 12 Digit	7818100520066

Dimensions

Dimension - B Length inch	2.46 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	192 mm
Dimension - Length Overall inch	7.55 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Pad Width inch	1.68 in
Dimension - Strip Length inch	2-19/32 in
Dimension - Z (inch)	1.98 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - ACSR Str Size	477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Size Range	477.0 (18/1) Pelican kcmil
Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	20
Minimum Pack Quantity	5
Pallet Quantity	1800

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YAS25R2N_LineArt](#)
[Sales Drawings - SE208417](#)
[Specifications - YAS361R2N](#)