

# Compression Terminal

By Burndy  
Catalog # [YAV0252M5](#)

HYLUG™ Copper tubing Compression terminals,1.5-2.5 mm2,M5 Stud, 2 Holes,Tin Plated.



## Application

Metric Wire Termination

## General

Connector Type	METRIC
Die Index	9
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637562
UPC 12 Digit	7818106375622

## Dimensions

Dimension - B Length inch	0.27 in
Dimension - Bolt Size fraction	#8-#10
Dimension - Bolt Size inch	0.21
Dimension - Hole Size fraction	#10
Dimension - Hole Size inch	0.21
Dimension - Hole Size mm	5.3 mm
Dimension - L Length Overall mm	44.7 mm
Dimension - Length Overall inch	1.76 in
Dimension - Pad Width inch	7.9 in
Dimension - Strip Length inch	0.28 in
Dimension - Stud Size fraction	#10
Dimension - Z inch	0.24 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	25 mm2
Conductor - Material	COPPER
Conductor Size	25 mm2
Conductor Type	CLASS 2

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50025887](#)