

Compression Terminal

By Burndy
Catalog # [YAV0252M8](#)

HYLUG™ Copper tubing Compression terminals, 25 mm², M8 Stud, 2 Holes, Tin Plated.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	9
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637685
UPC 12 Digit	7818106376855

Dimensions

Dimension - B Length inch	0.27 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	49.8 mm
Dimension - Length Overall inch	1.96 in
Dimension - Pad Width inch	11.0 in
Dimension - Strip Length inch	0.28 in
Dimension - Stud Size fraction	5/16
Dimension - Z inch	0.32 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	25 mm ²
Conductor - Material	COPPER
Conductor Size	25 mm ²
Conductor Type	CLASS 2

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	100
-----------------------	-----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50025887](#)