

YAV062M5, Compression Terminal

By Burndy

Catalog # [YAV062M5](#)

HYLUG™ Copper tubing Compression terminals, 4-6mm², M5 Stud, 2 Holes, Tin Plated.



Application

Metric Wire Termination

General

Catalog Number	YAV062M5
Connector Type	METRIC
Die Index	11
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637708
UPC 12 Digit	7818106377088

Dimensions

Dimension - B Length inch	0.41 in
Dimension - Bolt Size fraction	#8-#10
Dimension - Bolt Size inch	0.21
Dimension - Hole Size fraction	#10
Dimension - Hole Size inch	0.21
Dimension - Hole Size mm	5.3 mm
Dimension - L Length Overall mm	49.5 mm
Dimension - Length Overall inch	1.95 in
Dimension - Pad Width inch	9.5 in
Dimension - Strip Length inch	0.43 in
Dimension - Stud Size fraction	#10
Dimension - Z (inch)	0.26 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	4-6 mm ²
Conductor - Material	COPPER
Conductor Size	4-6 mm ²
Conductor Type	CLASS 2

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	100
-----------------------	-----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_yavm_lineart](#)
[Sales Drawings - 50025887](#)
[Specifications - YAV062M5](#)