

## YAV062M8, Compression Terminal

By Burndy  
Catalog # [YAV062M8](#)

HYLUG™ Copper tubing Compression terminals, 4-6mm<sup>2</sup>, M8 Stud, 2 Holes, Tin Plated.



### Application

Metric Wire Termination

### General

Catalog Number	YAV062M8
Connector Type	METRIC
Die Index	11
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637722
UPC 12 Digit	7818106377222

### Dimensions

Dimension - B Length inch	0.41 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	54.4 mm
Dimension - Length Overall inch	2.14 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	0.43 in
Dimension - Stud Size fraction	5/16
Dimension - Z (inch)	0.34 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper Str Size	4-6 mm <sup>2</sup>
Conductor - Material	COPPER
Conductor Size	4-6 mm <sup>2</sup>
Conductor Type	CLASS 2

### Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	100
-----------------------	-----

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_yavm\\_lineart](#)  
[Sales Drawings - 50025887](#)  
[Specifications - YAV062M8](#)