

Compression Terminal

By Burndy
Catalog # [YAV102M10](#)

HYLUG™ Copper tubing Compression terminals,10 mm2,M10 Stud, 2 Holes,Tin Plated.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	49
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637586
UPC 12 Digit	7818106375866

Dimensions

Dimension - B Length inch	0.44 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	83 mm
Dimension - Length Overall inch	3.27 in
Dimension - Pad Width inch	13.7 in
Dimension - Strip Length inch	0.43 in
Dimension - Stud Size fraction	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	10 mm2
Conductor - Material	COPPER
Conductor Size	10 mm2
Conductor Type	CLASS 2

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	100
-----------------------	-----

Product Assets

[3D Models - YAV102M10_MODEL-STEP](#)
[3D Models - YAV102M10_MODEL-PDF](#)
[3D Models - YAV102M10_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50025887](#)