

# Uninsulated Ring Terminal For 12 - 10 AWG

By Burndy  
Catalog # [YAV10H3BOX](#)



Uninsulated Ring Terminal For 12 - 10 AWG.

## Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors

## General

Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810532508

## Dimensions

Cable Insulation Diameter Maximum	0.192 in
Dimension - B Length fraction	22/71
Dimension - B Length inch	0.31 in
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size inch	0.27 in
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.17 in
Dimension - N inch	0.23 in
Dimension - Outside Diameter inch	0.21 in
Dimension - Pad Width inch	0.47 in
Dimension - Strip Length inch	7/16 in
Dimension - Stud Size inch	1/4 in
Dimension - Z inch	0.32 in

## Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50094162](#)  
[Technical Solutions - BURNDY\\_YAV10H3BOX\\_Specsheet](#)

