

Uninsulated Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [YAV10H4BOX](#)



Uninsulated Ring Terminal For 12 - 10 AWG.

General

Connector Type	Ring Terminal
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810021736

Dimensions

Cable Insulation Diameter Maximum	0.192 in
Dimension - B Length fraction	5/16 in
Dimension - B Length inch	0.31 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size fraction	2/5
Dimension - Hole Size inch	0.39 in
Dimension - L Length Overall mm	31 mm
Dimension - Length Overall inch	1.24 in
Dimension - N inch	0.28 in
Dimension - Outside Diameter inch	0.21 in
Dimension - Pad Width inch	0.55 in
Dimension - Strip Length inch	7/16 in
Dimension - Stud Size inch	3/8
Dimension - Z (inch)	0.44 in

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YAV10H25BOX_LineArt](#)
[Sales Drawings - 50094162](#)