



Uninsulated Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAV14T2BOX](#)



Copper Compression Lug, Heavy Duty, Ring Tongue, 1 Hole w/ Inspection Hole, 20-14 AWG, 1/4" Stud, Short Barrel, Tin Plated, Wire strip length: 9/32".

Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors, Industrials, Hospitals, Electric Utilities, Shipboard And Marine, Computers, Steel Mills, Mining Equipment And Other Equipment That Is Subject To Vibration Or Requiring Dependable Electrical Performance

General

| | |
|--------------------------------------|----------------------|
| Connector Type | Ring Terminal |
| EU RoHS Indicator | Yes |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Tongue Type | Ring |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Sub Brand | HYLUG |
| Trade Name | HYLUG™ |
| Type | Ring Tongue |
| UPC | 781810542507 |

Dimensions

| | |
|-----------------------------------|---------|
| Dimension - B Length fraction | 1/4 in |
| Dimension - B Length inch | 0.25 in |
| Dimension - Bolt Size fraction | 1/4 |
| Dimension - D inch | 0.42 in |
| Dimension - L Length Overall mm | 25 mm |
| Dimension - Length Overall inch | 0.99 in |
| Dimension - N inch | 0.25 in |
| Dimension - Outside Diameter inch | 0.16 in |
| Dimension - Pad Width inch | 0.42 in |
| Dimension - Strip Length inch | 9/32 in |
| Dimension - Stud Size inch | 0.25 |
| Dimension - Z (inch) | 0.32 in |

Conductor Related

| | |
|--|---|
| Conductor - Copper Solid Size | 20 AWG;18 AWG;17 AWG;16 AWG;15 AWG;14 AWG;13 AWG;12 AWG |
| Conductor - Copper Solid Size Range | 20 AWG-12 AWG |
| Conductor - Copper Str Aircraft Size | AN 20;AN 18;AN 16;AN 14 |
| Conductor - Copper Str Aircraft Size Range | AN 20-AN 14 |
| Conductor - Copper Str Size | 20 AWG;18 AWG;16 AWG;14 AWG |
| Conductor - Copper Str Size Range | 20 AWG - 14 AWG |
| Conductor Size | 16 - 14 AWG |
| Conductor Type | <ul style="list-style-type: none">CU C Solid-SizeCU C Str-Size |

Certifications And Compliance

| | |
|------------------------------------|-------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL486 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 1200 |
| Minimum Pack Quantity | 100 |
| Pallet Quantity | 99999 |

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YAV10T3BOX_LineArt](#)
[Sales Drawings - 50094160](#)





A proud member of the Hubbell Family.

BRDY-YAV14T2BOX-SPEC-EN | REV 5/2024