

YAV1502M10, Compression Terminal

By Burndy
Catalog # YAV1502M10



Non Insulated Cu Tubular Terminal, 2 Hole, W/Insp Window, 150 mm, 10 mm Stud, 4.20 IN L, Compression, 17 Index, 27 mm Strip Length.

Application

Metric Wire Termination

General

Catalog Number	YAV1502M10
Connector Type	METRIC
Die Index	17
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810442722
UPC 12 Digit	7818104427222

Dimensions

Dimension - B Length inch	26.2 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	107 mm
Dimension - Length Overall inch	4.20 in
Dimension - Pad Width inch	30.5 in
Dimension - Strip Length inch	1.06 in
Dimension - Stud Size fraction	3/8
Dimension - Z (inch)	0.42 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	150 mm ²
Conductor - Material	COPPER
Conductor Size	150 mm ²
Conductor Type	CLASS 2

Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	9600

Product Assets

- [3D Models - YAV1502M10_MODEL-PDF](#)
- [3D Models - YAV1502M10_MODEL-STEP](#)
- [3D Models - YAV1502M10_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_yavm_lineart](#)
- [Sales Drawings - 50025887](#)
- [Specifications - YAV1502M10](#)