

# YAV1502M16, Compression Terminal

By Burndy  
Catalog # [YAV1502M16](#)

HYLUG™ Copper tubing Compression terminals,150 mm,M16 Stud, 2 Holes,Tin Plated.



## Application

Metric Wire Termination

## General

Catalog Number	YAV1502M16
Connector Type	METRIC
Die Index	17
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638262
UPC 12 Digit	7818106382622

## Dimensions

Dimension - B Length inch	26.2 in
Dimension - Bolt Size fraction	5/8
Dimension - Bolt Size inch	0.63
Dimension - Hole Size fraction	5/8
Dimension - Hole Size inch	0.69
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	119 mm
Dimension - Length Overall inch	4.70 in
Dimension - Pad Width inch	30.5 in
Dimension - Strip Length inch	1.06 in
Dimension - Stud Size fraction	5/8
Dimension - Z (inch)	0.67 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	150 mm2
Conductor - Material	COPPER
Conductor Size	150 mm2
Conductor Type	CLASS 2

## Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	10
-----------------------	----

## Product Assets

- [3D Models - YAV1502M16\\_MODEL-PDF](#)
- [3D Models - YAV1502M16\\_MODEL-IGES](#)
- [3D Models - YAV1502M16\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_yavm\\_lineart](#)
- [Sales Drawings - 50025887](#)
- [Specifications - YAV1502M16](#)