

# Compression Terminal

By Burndy  
Catalog # [YAV150F2M20](#)

Cu Compression Metric Lug, 2 Hole, W/Inspection Window, 150 mm, M20 Stud, 44.5 mm Spacing, Standard Barrel, 29 mm Wire Strip Length.



## Application

Metric Wire Termination

## General

Connector Type	METRIC
Die Index	17
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810640920
UPC 12 Digit	7818106409200

## Dimensions

Dimension - B Length inch	1.06 in
Dimension - Bolt Size fraction	7/8
Dimension - Bolt Size inch	0.88
Dimension - Hole Size fraction	7/8
Dimension - Hole Size inch	0.94
Dimension - Hole Size mm	23.8 mm
Dimension - L Length Overall mm	132 mm
Dimension - Length Overall inch	5.20 in
Dimension - Pad Width inch	1.29 in
Dimension - Strip Length inch	1.14 in
Dimension - Stud Size fraction	7/8
Dimension - Z inch	0.89 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	150 mm <sup>2</sup>
Conductor - Material	COPPER
Conductor Size	150 mm <sup>2</sup>
Conductor Type	CLASS 2

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	10
-----------------------	----

## Product Assets

[3D Models - YAV150F2M20\\_MODEL-STEP](#)  
[3D Models - YAV150F2M20\\_MODEL-IGES](#)  
[3D Models - YAV150F2M20\\_MODEL-PDF](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50025888](#)