

Compression Terminal

By Burndy
Catalog # [YAV150M8](#)

Compression terminal HYLUG™ Copper tubing, 1 Hole, 150 mm, M8 Stud, Tin Plating.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	17
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637517
UPC 12 Digit	7818106375177

Dimensions

Dimension - B Length inch	1.03 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	58.7 mm
Dimension - Length Overall inch	2.31 in
Dimension - Pad Width inch	1.2 in
Dimension - Strip Length inch	1.06 in
Dimension - Stud Size fraction	5/16
Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	150 mm ²
Conductor - Material	COPPER
Conductor Size	150 mm ²
Conductor Type	CLASS 2

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Minimum Pack Quantity	10

Product Assets

[3D Models - YAV150M8_MODEL-PDF](#)
[3D Models - YAV150M8_MODEL-STEP](#)
[3D Models - YAV150M8_MODEL-IGES](#)
[Sales Drawings - 50025521](#)