

Compression Terminal

By Burndy
Catalog # YAV16M4

Compression terminal HYLUG™ Copper tubing; 1 Hole; 16 mm2;
M4 Stud; Tin Plating.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	7
Finish Type	Tin-Plated
Material	COPPER
Plated	YES
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637494
UPC 12 Digit	7818106374944

Dimensions

Dimension - B Length inch	0.50 in
Dimension - Bolt Size fraction	#8
Dimension - Hole Size fraction	#8
Dimension - Hole Size inch	0.18
Dimension - Hole Size mm	4.6 mm
Dimension - L Length Overall mm	31.5 mm
Dimension - Length Overall inch	0.09 in
Dimension - Pad Width inch	0.48 in
Dimension - Strip Length inch	0.51 in
Dimension - Stud Size fraction	#8
Dimension - Z (inch)	0.29 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	16 mm2
Conductor - Material	COPPER
Conductor Size	16 mm2
Conductor Type	CLASS 2

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	50
Minimum Pack Quantity	50

Product Assets

[3D Models - YAV16M4_MODEL-PDF](#)
[3D Models - YAV16M4_MODEL-IGES](#)
[3D Models - YAV16M4_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_yavm_lineart](#)
[Sales Drawings - 50025521](#)