

YAV18T19FBOX, Uninsulated Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # YAV18T19FBOX



Uninsulated Fork Terminal For 22 - 18 AWG.

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors

General

Catalog Number	YAV18T19FBOX
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Fork Tongue
UPC	781810533987
UPC 12 Digit	7818105339877

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.27 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - D inch	0.50 in
Dimension - L Length Overall mm	21 mm
Dimension - Length Overall inch	0.84 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.12 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#4;#5;#6
Dimension - Z (inch)	0.25 in

Conductor Related

Conductor - Copper Str Aircraft Size	AN 22;AN 20;AN 18
Conductor - Copper Str Aircraft Size Range	AN 22-AN 18
Conductor - Copper Str Size	22 AWG;20 AWG;18 AWG
Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_tfla](#)
[Sales Drawings - 50094187](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAV18T19FBOX-SPEC-EN | REV 8/2024