

# YAV1CLTC38FX, Compression Terminal, 1 Flex G,H,I,K,M,DLO, 1 AWG B/C, Cu, 1-Hole, 3/8" Stud, Standard Barrel



By Burndy  
Catalog # [YAV1CLTC38FX](#)

1 Flex G,H,I,K,M,DLO, 1 AWG (B/C) CU, One Hole, 3/8 Stud Size, Standard Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Green Color Code, 11 or 375 Die Index.

## Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connections are clearly marked with stamping and barrel color coding

## Application

Wire Termination

## General

Catalog Number	YAV1CLTC38FX
Color Code	Green
Connector Type	STANDARD BARREL
Die Index	11
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810022924
UPC 12 Digit	7818100229244

## Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.62 in

Dimension - Bolt Hole Size inch	0.41 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	47 mm
Dimension - Length Overall inch	1.84 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	11/16 in
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8
Dimension - Z (inch)	0.42 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size	1 AWG
Conductor - Copper DLO Size Range	1 AWG
Conductor - Copper Flex G Size	"1 AWG"
Conductor - Copper Flex G Size Range	1 AWG
Conductor - Copper Flex H Size	"1 AWG"
Conductor - Copper Flex H Size Range	1 AWG
Conductor - Copper Flex I Size	"1 AWG"
Conductor - Copper Flex I Size Range	1 AWG
Conductor - Copper Flex K Size	"1 AWG"

Conductor - Copper Flex K Size Range	1 AWG
Conductor - Copper Flex M Size	"1 AWG"
Conductor - Copper Flex M Size Range	1 AWG
Conductor - Copper Solid Size	1 AWG
Conductor - Copper Solid Size Range	1 AWG
Conductor - Copper Str Compact Size	"1 AWG"
Conductor - Copper Str Navy Size	75
Conductor - Copper Str Navy Size Range	75 (37) Navy
Conductor - Copper Str Size	"1 AWG"
Conductor - Copper Str Size Range	1 AWG
Conductor - Material	COPPER
Conductor Size	1 AWG
Conductor Type	CODE/FLEX
Wire Size	1 AWG

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	48000

### Product Assets

- [3D Models - YAV1CLTC38FX\\_MODEL-STEP](#)
- [3D Models - YAV1CLTC38FX\\_MODEL-IGES](#)
- [3D Models - YAV1CLTC38FX\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE..208001-01](#)
- [Specifications - YAV1CLTC38FX](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

